

ProductSheet

# HyperX OMEN MAX 16 inch Gaming Laptop PC 16-ak1000AX (D91K4PA)



**Claim the power. Master the speed.**

The HyperX OMEN MAX 16 gaming laptop provides unparalleled performance both at-home or on-the-go. With NVIDIA® GeForce RTX™ 50 Series GPUs and AMD Ryzen™ AI CPUs[1], a new Unleashed Mode for manual overclocking, and a thermal architecture built to cut down on both throttling and long term wear, dedicated gamers can achieve their best for years to come.

#### Performance you control

Throttle less and carry more with the latest AMD Ryzen™ AI CPUs[1] and NVIDIA® GeForce RTX™ 50 Series GPUs.

#### Put your throttling on ice

Self-cleaning fans, a vapor chamber, and liquid metal ensure your laptop stays cool and reduces maintenance.

#### Claim the competitive advantage

Get a device that moves at the speed of your reactions with our new HyperAction 1000Hz polling rate keyboard.

### Featuring

#### Get a fresh perspective

From a rejuvenated Start menu, to new ways to connect to your favorite people, news, games, and content—Windows 11 is the place to think, express, and create in a natural way. [2]

#### AMD Ryzen™ AI 400 Series HX processors

Ryzen™ AI 400 Series HX processors offer strong multithreaded compute, integrated Radeon™ graphics, and efficient operation to support versatile PCs spanning productivity, creation, and portable performance systems. [3]

#### Game Changer

Powered by NVIDIA Blackwell, GeForce RTX™ 50 Series Laptop GPUs bring game-changing AI capabilities to gamers and creators. Multiply performance with NVIDIA DLSS 4, generate images at unprecedented speed, and unleash your creativity with NVIDIA Studio. [4]

#### OLED display

With display technology that lights each pixel separately, you'll get deeper blacks for richer contrast, enhanced color depth, and more power efficiency than traditional LED screens.

#### Eyesafe® Certified Display

Eyesafe® certified displays meet TÜV low blue light requirements and Eyesafe® standards for protecting your eyes from harmful blue light without distorting colors to reduce eyestrain when working for long periods of time. [5]



## Specifications

<b>Operating System Software</b>	Windows 11 Home
<b>Product Color Description (fixed)</b>	Shadow black aluminum
<b>Product Design</b>	Sandblasted and paint finish
<b>Processor Family</b>	AMD Ryzen™ AI 9 processor
<b>Processor Name</b>	AMD Ryzen™ AI 9 HX 475 (up to 5.2 GHz max boost clock, 24 MB L3 cache, 12 cores, 24 threads) <sup>[6,7]</sup>
<b>Chipset</b>	AMD integrated SoC
<b>Standard Memory Description 01</b>	32 GB DDR5-5600 MT/s (2 x 16 GB)
<b>Hard Drive Description (01)</b>	1 TB PCIe® Gen5 NVMe™ M.2 SSD
<b>Graphics Card Segment 01</b>	Integrated
<b>GScardseg 01 Available Card 01</b>	AMD Radeon™ 890M Graphics
<b>Display Description (metric)</b>	40.6 cm (16") diagonal, 2.5K (2560 x 1600), OLED, up to 240 Hz, 0.2 ms response time, UWVA, micro-edge, BrightView, Low Blue Light, SDR 500 nits, HDR 1100 nits, 100% DCI-P3
<b>Display Description</b>	16" diagonal, 2.5K (2560 x 1600), OLED, up to 240 Hz, 0.2 ms response time, UWVA, micro-edge, BrightView, Low Blue Light, SDR 500 nits, HDR 1100 nits, 100% DCI-P3
<b>Screen-To-Body Ratio (without speakers)</b>	89% <sup>[18]</sup>
<b>Audio Features</b>	DTS:X® Ultra; Dual speakers; HP Audio Boost; HyperX
<b>Product Dimensions (metric)</b>	35.65 x 26.9 x 2.29 cm (front); 35.65 x 26.9 x 2.48 cm (rear)
<b>Product Dimensions (imperial)</b>	14.04 x 10.59 x 0.9 in (front); 14.04 x 10.59 x 0.98 in (rear)
<b>Weight (metric)</b>	2.78 kg
<b>Weight (imperial)</b>	6.13 lb
<b>Package Dimensions (metric)</b>	9.4 x 42.8 x 33.2 cm
<b>Package Dimensions (imperial)</b>	3.7 x 16.85 x 13.07 in
<b>Package Weight (metric)</b>	5.33 kg
<b>Package Weight (imperial)</b>	11.77 lb
<b>Keyboard</b>	Full-size, per key RGB backlit, shadow black keyboard with numeric keypad and NKRO Anti-Ghosting Key technology
<b>Pointing Device</b>	HP Imagepad
<b>Sensors</b>	IR thermal sensor
<b>Camera</b>	HP True Vision 1080p FHD IR camera with temporal noise reduction and integrated dual array digital microphones
<b>External I/O Ports</b>	2 USB Type-A 10Gbps signaling rate; 1 AC smart pin; 1 HDMI 2.1; 1 headphone/microphone combo; 1 RJ-45; 2 USB Type-C® 40Gbps signaling rate (USB Power Delivery 3.1, DisplayPort™ 2.1, HP Sleep and Charge) <sup>[19,42]</sup>
<b>Network Interface</b>	Integrated 10/100/1000/2500 GbE LAN
<b>Wireless Technologies</b>	MediaTek Wi-Fi 7 MT7925 (2x2) and Bluetooth® 6.0 wireless card <sup>[12,46]</sup>
<b>Power Supply Type</b>	420 W AC GaN power adapter
<b>Battery Type</b>	6-cell, 83 Wh Li-ion polymer <i>([23])</i>
<b>Battery Recharge Time</b>	Supports battery fast charge: approximately 50% in 30 minutes <sup>[5]</sup>
<b>Sustainable Impact Specifications</b>	Ocean-bound plastic in bezel; Recycled metal in cover, base and hinge cap(s); Keyboard keycaps, scissors and keyboard plate contain post-consumer recycled materials
<b>Security Management</b>	Camera privacy shutter; Trusted Platform Module (Firmware TPM) support
<b>Software Included</b>	McAfee Online Protection 30-day trial
<b>Software - Productivity &amp; Finance</b>	1 month trial for new Microsoft 365 customers <sup>[24,50]</sup>
<b>Cloud Service</b>	100 GB Dropbox storage for 3 months <sup>[1]</sup>
<b>UPC Number</b>	821844567067

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed. Max Boost clock frequency performance varies depending on hardware, software and overall system configuration. Features and software that require a NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Potential NPU interfering performance varies by use, configuration, software and other factors.

[2] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[3] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[4] ©2025 NVIDIA Corporation. NVIDIA, the NVIDIA logo, GeForce, and GeForce RTX are registered trademarks and/or trademarks of NVIDIA Corporation in the United States and other countries. All other trademarks and copyrights are the property of their respective owners.

[5] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower. Eyesafe® Display for Low Blue Light is the Display Compliance Test Specification quality. See <https://eyesafe.com> for more details. Display measured diagonally

## Technical Specifications Footnotes

[1] 100 GB of free Dropbox storage for 3 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at <https://www.dropbox.com/help/space/hp-promotion>. Internet service required and not included.

[5] Recharges your battery up to 50% within 30 minutes when the system is off using "shut down" command, using HP adapter provided with the notebook or recommended power adapter disclosed in specifications (see <http://store.hp.com>). After charging has reached 50% capacity, charging speed will return to normal speed. Charging time may vary +/-10% due to System tolerance. Available on select HP products.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[7] Max Boost clock frequency performance varies depending on hardware, software and overall system configuration.

[12] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires Windows 11 2024, select Intel® Core™ or Intel® Core™ Ultra processor, and a Wi-Fi 7 router, sold separately. Wi-Fi 7 is backwards compatible with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices.

[18] Percent of active plus nonactive viewing area to active viewing area plus border. Measure with lid vertical to the desk.

[19] For best results with HP Sleep and Charge, use a USB charging protocol standard cable or cable adapter with an external device.

[24] Must activate within 180 days of Windows activation.

[42] For optimal performance and battery chargeability while gaming and rendering, use the power adapter that ships with the PC. You can use the 100W/20V Type-C adapter or power bank when running light loading tasks. System-off charging is only supported on 20V Type-C adapter or power bank.

[46] Bluetooth® 6.0 operation requires Microsoft OS/Chrome OS support. Until Microsoft OS/Chrome OS support is available, Bluetooth® 6.0 will function as Bluetooth® 5.4 or lower.

---

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Optane, Celeron, Pentium, Iris, XMM, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD, Ryzen, Athlon, and Radeon are trademarks of Advanced Micro Devices, Inc. Qualcomm and Snapdragon are trademarks or registered trademarks of Qualcomm Technologies, Inc. and/or its subsidiaries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. McAfee and McAfee LiveSafe are trademarks or registered trademarks of McAfee LLC in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

