


# ThinkPad P14s Gen 6 (AMD)

Designed to empower advanced business professionals, this workstation, powered by the AMD Ryzen™ AI 9 PRO 300 Series Processor, offers unparalleled performance, efficiency, and AI readiness. With support for up to 12 high-performance cores, the processor ensures seamless multitasking, rapid data processing, and smooth handling of resource-intensive applications. Integrated AMD Radeon™ 840M, 860M, and 890M graphics provide sharp visuals and smooth rendering, allowing professionals to efficiently tackle visually demanding tasks without the need for a discrete GPU. Additionally, support for up to four independent displays via dual Thunderbolt™ 4 ports and an HDMI® port creates an expansive, customizable workspace, ideal for multitasking across dashboards, data visualizations, video conferencing, and productivity tools.



**Elevate Professional Endeavors  
with Powerhouse Workstations**


This workstation, equipped with 2W dual Dolby Atmos® stereo speakers, delivers immersive sound quality, making it perfect for virtual meetings, media consumption, and presentations. The optional 5.0MP camera, featuring an IR sensor and privacy shutter, ensures crystal-clear video conferencing while preserving privacy when not in use. The Ultrasonic Human Presence Detection feature further enhances convenience by automatically activating the system when the user is present and conserving energy when absent. Plus, the fixed-focus camera, paired with temporal noise reduction, guarantees consistent and clear video quality, even in low-light environments.

Unlock faster insights, uninterrupted multitasking, and the graphical edge you need for data-driven decisions. Powered by the AMD Ryzen™ AI 9 PRO 300 Series Processor with up to 12 cores, this workstation delivers the multi-threaded performance required to handle complex calculations, model forecasts, and run simulations without lag. Paired with integrated AMD Radeon™ 840M, 860M, or 890M graphics, it ensures smooth, high-resolution rendering of data dashboards, charts, and statistical outputs – even across multiple displays.

Whether you're retouching high-res images or working on complex multilayer compositions, integrated AMD Radeon™ 840M, 860M, and 890M graphics deliver the performance you need to stay in your creative flow. These GPUs are optimized for content creation tools like Adobe Photoshop, offering faster rendering, smoother zooming, and real-time layer manipulation.

## Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

## Accessories

### Lenovo 15.6-inch Laptop Casual Backpack B210 Grey

- Extra cushioning and padding for maximum comfort
- Waterproof fabric to keep your gadgets dry and safe
- Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

### Lenovo Go 130W Multi-Port Charger

- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection



PN: GOA6130WUS, GOA6130WEU, GOA6130WUK

# ThinkPad P14s Gen 6 (AMD)

## Performance

### Processor

AMD Ryzen AI 5/7/9 PRO 300 Series Processor

### Operating System\*

Windows 11 Pro  
Windows 11 Home  
Fedora Linux  
Ubuntu Linux LTS  
Red Hat Enterprise Linux (certified only)

### NPU

Integrated AMD Ryzen AI, up to 50 TOPS

### Graphics

AMD Radeon 840M (integrated)  
AMD Radeon 860M (integrated) AMD Radeon 890M (integrated)

### Memory

Up to 96GB, 2x SO-DIMM

### Storage<sup>1</sup>

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

<sup>1</sup>The storage capacity supported is based on the test results with current Lenovo storage offerings.

### Audio

High Definition (HD) Audio  
Stereo speakers, 2W x2, Dolby Atmos  
Dual-microphone array, 360° far-field, Dolby Voice\*

### Camera\*

5.0MP + IR, with privacy shutter and optional Ultrasonic Human Presence Detection, temporal noise reduction  
5.0MP with privacy shutter, temporal noise reduction

### Battery<sup>2</sup>

52.5Wh or 57Wh battery, Rapid Charge

<sup>2</sup>Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

### Power Adapter\*

65W USB-C adapter, PD 3.0  
65W USB-C nano GaN adapter, PD 3.0  
65W USB-C slim GaN adapter, PD 3.0

## Design

### Display<sup>3</sup>

14" WUXGA (1920x1200) IPS Anti-glare 16:10  
- 400nits, 45% NTSC  
- 400nits, 45% NTSC, on-cell touch  
- 500nits, 100% sRGB, low power, Eyesafe  
- 500nits, 100% sRGB, on-cell touch, ThinkPad Privacy Guard  
14" 2.8K (2880x1800) OLED AGARAF 16:10  
- 500nits, 100% DCI-P3, Add-on Film touch, Eyesafe

<sup>3</sup>IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

### Keyboard

6-row, spill-resistant, Copilot key, optional backlight

### Touchpad

TrackPoint and glass-like Mylar surface 3-button  
Trackpad  
61 x 115 mm (2.40 x 4.53 inches)

### Dimensions<sup>4</sup>

WWAN support models:  
315.9 x 223.7 x 10.9/16.13 (front/rear), 21.95 (maximum) mm;  
12.44 x 8.81 x 0.43/0.64 (front/rear), 0.86 (maximum) inches  
Non-WWAN models:  
315.9 x 223.7 x 10.9/16.13 (front/rear), 21.8 (maximum) mm;  
12.44 x 8.81 x 0.43/0.64 (front/rear), 0.86 (maximum) inches

<sup>4</sup>The system dimensions may vary depending on configurations.

### Weight<sup>5</sup>

Starting at 1.39 kg (3.06 lbs)

<sup>5</sup>The system weight is approximate and may vary depending on configurations

### Color

Black

### Case material

PC + 20% CF + 50% GF + 30% PCC (top), PC + 50% GF + 45% PCC (bottom)  
PC + 20% CF + 50% GF + 30% PCC (top), PC + 20% CF + 30% PCC (bottom)

## Connectivity

### Ethernet

Gigabit onboard Ethernet

### WLAN + Bluetooth\*<sup>6</sup>

MediaTek Wi-Fi 7 MT7925, 802.11be, Bluetooth 5.4

<sup>6</sup>Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

### WWAN\*

Up to 5G with embedded eSIM\*

### NFC

Near Field Communication\*

### Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)  
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On  
1x HDMI 2.1, up to 4K/60Hz  
1x Headphone / microphone combo jack (3.5mm)  
1x Ethernet (RJ-45)  
1x Security keyhole  
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 1.4  
1x Smart card reader\*  
1x Nano-SIM card slot\*

### Docking

Docking support via Thunderbolt or USB-C

## Security & Privacy

### Security

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0  
Kensington Nano Security Slot  
Smart card reader\*  
Touch style MOC fingerprint reader\*  
Camera privacy shutter\*  
IR camera for Windows Hello (facial recognition)\*  
Ultrasonic Human Presence Detection\*

## Manageability

### System Management\*

AMD PRO Manageability

## Certifications

### Green Certifications<sup>7 8 9</sup>

ENERGY STAR 9.0  
EPEAT Gold Registered  
TCO Certified 10.0  
RoHS compliant

<sup>7</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>8</sup>EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

<sup>9</sup>EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.

### Other Certifications

Eyesafe Certified\*  
Low Blue Light\*  
MIL-STD-810H