

ThinkPad X1 Carbon Gen 13 Aura Edition

With efficient performance, stunning visuals, and uncompromising security this ThinkPad empowers professionals to stay productive and connected no matter where work takes them. With up to Intel® V Series Core Ultra 7 Processor, it effortlessly tackles complex tasks, from processing large datasets to running high-demand applications. The option for Intel Arc Graphics elevates the experience for users who rely on graphics-intensive software, delivering smooth visuals for editing, rendering, or presentations.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkPad X1 series laptops are chosen by professionals for their durability, portability, and powerful performance. With high-resolution displays, robust processors, and extensive connectivity options, they excel in productivity tasks.

Its 14" 2.8K resolution display with an optional Add-on Film touch feature provides vibrant visuals and responsive interaction, perfect for virtual collaboration or immersive presentations. The touch functionality enhances productivity by making the device highly interactive, offering an intuitive experience that improves workflow and engagement.

Built with Intel Wi-Fi 7 support, it keeps users connected even in bandwidth-intensive environments, ensuring smooth access to cloud applications, data, and real-time communication. With versatile connectivity options DisplayPort™, and Thunderbolt 4 / USB4® ports—connecting to different devices and setups becomes effortless.

With HD Audio, stereo speakers, and a dual-microphone array featuring Dolby Atmos, it ensures crystal-clear, immersive web conferencing, capturing voices with precision—even from a distance.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo Wireless VoIP Headset

- Versatile control buttons for seamless functionality
- Advanced microphone with noise cancellation technology
- Extended battery life for uninterrupted listening experience



PN: 4XD1M80020 (Lenovo Wireless VoIP Headset), 4XH1M80022 (Lenovo USB-A Bluetooth® Audio Receiver Gen 2), 4XD1M80021 (Lenovo Wireless VoIP Headset Earcup)

Lenovo USB-C Dual Display Travel Dock

- Enhanced connectivity and visual experience in a portable hub
- Continuous power supply; efficient charging solution for mobile devices
- Eco-friendly dual display travel dock; style meets sustainability



PN: Dock without Adapter : 40B90000WW, Dock with Adapter : 40B90100xx



ThinkPad X1 Carbon Gen 13 Aura Edition

Performance

Processor Intel V Series Core Ultra 5 / 7 Processor (Series 2) - Lunar Lake Intel U or H Series Core Ultra 5 / 7 Processor (Series 2) - Arrow Lake
AI PC Category* AI PC (Arrow Lake) Copilot+ PC (Lunar Lake)
Operating System* Windows 11 Pro or Home Fedora or Ubuntu Linux
NPU* Integrated Intel AI Boost, up to 48 TOPS
Graphics Intel Graphics (integrated) Intel Arc 130T GPU (integrated) Intel Arc 140T GPU (integrated) Intel Arc Graphics 130V (integrated) Intel Arc Graphics 140V (integrated)
Memory Arrow Lake: 16GB, 32GB or 64GB LPDDR5X-8400, soldered Lunar Lake: 16GB or 32GB LPDDR5X-8533 MoP memory, soldered
Storage Up to 1x 2TB M.2 2280 PCIe NVMe SSD
Audio* Arrow Lake: High Definition (HD) Audio Lunar Lake: SoundWire Stereo speakers, 2W x2, Dolby Atmos Dual-microphone array, 360° far-field, Dolby Voice
Camera* FHD 1080p + IR discrete, with privacy shutter, temporal noise reduction UHD 8.0MP + IR discrete, with privacy shutter, MIPI, Computer Vision, temporal noise reduction
Battery 57Wh (up to 17.11 hr) battery, Rapid Charge
Power Adapter* 65W USB-C adapter, PD 3.0 65W USB-C nano GaN adapter, PD 3.0 65W USB-C slim adapter, PD 3.0 65W USB-C slim GaN adapter, PD 3.0

Design

Display 14" WUXGA (1920x1200) IPS Anti-glare 16:10 - 500nits, 100% sRGB, low power, Eyesafe - 500nits, 100% sRGB, low power, touch, Eyesafe - 500nits, 100% sRGB, ThinkPad Privacy Guard, Eyesafe 14" 2.8K (2880x1800) OLED AGARAS 16:10 - 400nits, 100% DCI-P3, 120Hz, DisplayHDR True Black 500, Dolby Vision, Eyesafe - 500nits, 100% DCI-P3, 120Hz VRR, DisplayHDR True Black 500, Dolby Vision, Eyesafe - 500nits, 100% DCI-P3, 120Hz VRR, Add-on film touch, DisplayHDR True Black 500, Dolby Vision, Eyesafe
Screen-to-Body Ratio 89.2%
Keyboard 6-row, spill-resistant, air intake design, Copilot key, backlight
Touchpad TrackPoint and glass surface Haptic Touchpad 70.5 x 120 mm (2.78 x 4.72 inches) TrackPoint and glass surface 3-button Trackpad 56.2 x 120 mm (2.21 x 4.72 inches)
Dimensions Starting at 312.80 x 214.75 x 8.08/14.37 (front/rear), 16.95 (maximum) mm; 12.31 x 8.45 x 0.32/0.56 (front/rear), 0.67 (maximum) inches
Weight Arrow Lake: starting at 1006 g (2.22 lbs) Lunar Lake: starting at 986 g (2.17 lbs)
Color Black, paint Black, paint, FIFA Edition Black, weave
Case material Carbon fiber (top), magnesium or aluminium (bottom)
Connectivity
WLAN + Bluetooth* Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3 Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4
WWAN* 4G LTE CAT16 with embedded eSIM 5G Sub-6 GHz with embedded eSIM

NFC

Near Field Communication*

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 15-65W & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt / USB-C

Security & Privacy

Security

ThinkShield
Discrete TPM 2.0
Kensington Nano Security Slot
Touch style MOC fingerprint reader
Camera privacy shutter
IR camera for Windows Hello (facial recognition)
Ultrasonic Human Presence Detection*
Computer Vision-based Human Presence Detection*
Privacy Guard with Privacy Alert*

Manageability

System Management*

Intel vPro Enterprise*

Environmental

Material

Recycled carbon fiber contained in plastic frame on top cover
90% recycled magnesium on keyboard frame
90% recycled magnesium or 45% hydro aluminum on bottom cover
85% PCC recycled plastic used in keycaps of backlit keyboard
90% PCC recycled plastic used in speaker enclosure
90% PCC recycled plastic used in the 57Wh battery pack enclosure
90% PCC recycled plastic used in 65W adapters
35% PCC recycled plastic used in cable / antenna holders
25% PCC recycled plastic used in hall sensor magnet
Plastic free packaging with FSC certified paper

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2026 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.