

DVI Video Splitter

2/4-Port DVI Video Splitter with Audio



FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- · Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver
 is connected
- · Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.



Table of Contents

Introduction	1
Packaging Contents	1
System Requirements	1
Top View - ST122DVIA	2
Rear View - ST122DVIA	2
Front View - ST124DVIA	3
Rear View - ST124DVIA	3
Installation	4
Installation Hardware Installation	
	4
Hardware Installation	4 5
	4 5



Introduction

The StarTech.com DVI Splitter with Audio lets you share one DVI video and audio source on two (ST122DVIA) or four (ST124DVIA) displays and also act as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10m) away. A simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, health care, professional A/V, control centres, retail POS environments), the DVI splitter/distribution amplifier is easy to install and supports high definition resolutions up to 1080p or 1920x1200 for computers.

Packaging Contents


- 1 x ST122DVIA/ST124DVIA video splitter
- 1 x Rack Mounting brackets (ST124DVIA only)
- 1 x Power Adapter
- 1 x Instruction Manual

System Requirements


- · DVI enabled video source
- DVI enabled display devices
- Analog stereo audio source with 3.5mm mini-plug interface (optional)
- Analog stereo speakers with 3.5mm mini-plug interface (optional)



Top View - ST122DVIA



Rear View - ST122DVIA






Front View - ST124DVIA



Rear View - ST124DVIA






Installation

Hardware Installation

- 1. Make sure all devices are powered off and unplugged.
- Connect the DVI video source (i.e. computer, HDTV box, etc.) to the Input connector on the splitter, using a standard male/male DVI cable. If using audio, also connect a 3.5mm mini-jack audio cable from the video source to the Input connector on the splitter.
- NOTE: Use of DVI-D cables is recommended as some DVI video sources may default to using an analog signal, when a DVI-I cable is used.
- 4. Connect the DVI display device (i.e. monitor, HDTV, projector, etc.) to one of the Output connectors on the splitter, using standard male/male DVI cables. If using audio, also connect a 3.5mm minijack audio cable from the Output connector to the display device/speakers.
- 5. Repeat for each display device or port on the splitter.



- Power on the display devices first. At least one display device must be connected to the splitter, before powering it on, to ensure proper operation.
- Connect power to the DVI splitter to power it on. The Power LED will light up green.



8. Power on the video source device. The Power LED should change to blue to indicate it is receiving a good input signal.

Driver Installation

No driver installation is required to use the DVI video splitter, as it is an external, hardware-only device, that will not be seen by the host system.



Specifications

	ST122DVIA	ST124DVIA
Video Signal	DVI-D (digital)	
Number of Ports	2	4
Connectors	3 x 24-pin DVI-I 3 x 3.5mm mini-jack 1 x DC Power	5 x 24-pin DVI-I 5 x 3.5mm mini-jack 1 x DC Power
LEDs	1 x Power/Input 2 x Output Link	1 x Power/Input 4 x Output Link
Maximum Video Resolution	1920x1200@60Hz	
Maximum Distance	10m / 33ft	
Maximum Video Bandwidth	350MHz	
HDCP Compliant	Yes (1.1)	
Power Adapter	9VDC, 600mA, center positive	
Operating Temperature	0°C ~ 40°C (32°F ~ 104°F)	
Storage Temperature	-20°C ~ 60°C (-4°F ~ 140°F)	
Humidity	0 ~ 80% RH	
Dimensions	181.4mm x 85.2mm x 20.0mm	220.0mm x 135.0mm x 44.0mm
Weight	600g	1100g



Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

Warranty Information

This product is backed by a one year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.



StarTech.com has been making "hard-to-find easy" since 1985, providing high quality solutions to a diverse IT and A/V customer base that spans many channels, including government, education and industrial facilities to name just a few. We offer an unmatched selection of computer parts, cables, A/V products, KVM and Server Management solutions, serving a worldwide market through our locations in the United States, Canada, the United Kingdom and Taiwan.

Visit www.startech.com today for complete information about all our products and to access exclusive interactive tools such as the Cable Finder, Parts Finder and the KVM Reference Guide.