

8 Port Unmanaged Gigabit Ethernet PoE+ PSE Switch - 30W per Port

IES81000POE



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Product Diagram	1
Front View	1
Rear View	1
Introduction	2
Packaging Contents	2
LED Indicators	2
Installation	3
Wall-Mounting	3
Hardware Installation	3
Specifications	4
Technical Support	5
Warranty Information	5

Product Diagram

Front View



Rear View



Introduction

Packaging Contents

- 1 x Gigabit Ethernet PoE Switch
- 4 x Mounting Screws
- 2 x Wallmount Brackets
- 1 x Set, Rubber Feet
- 1 x Universal Power Adapter
- 3 x Power Cords (NA /UK /EU)
- 1 x Instruction Manual

LED Indicators

LED	Function
Power (1)	Solid - power is on and normal
ACT (Per Port, 8 total)	On – Port is connected
	Off – No connection
10/100M (Per Port, 8 total)	On – Connected at 100Mbps
	Off - Connected at 10Mbps
1000M (Per Port, 8 total)	On – Connected at 1000Mbps
PoE (Per Port, 8 total)	On - Power over Ethernet function is enabled
	Off - PoE function is disabled, behaving as a regular LAN port

Installation

Wall-Mounting

1. Attach the wall mount brackets to the switch (one per side) using the screws provided.
2. Depending on the mounting surface, use the appropriate hardware to mount to the wall surface.

Hardware Installation

1. Plug one end of the power adapter into an open electrical outlet and the other into the DC connector on the rear panel of the Network Switch. The Power LED on the front of the Switch should now be lit.
2. Connect a network cable to port 1 on the front panel of the switch, and connect the other end of the cable into the RJ-45 port on your upstream switch or router. The connection speed should auto-detect and the appropriate LEDs will illuminate to show activity.
3. Connect your PoE or non-PoE devices to the remaining ports on the switch (e.g. computer, IP Phone, IP Camera, etc.). The switch will auto-detect connection speed and whether PoE is required, and the appropriate LEDs will illuminate and show activity.

Specifications

Number of Ports	8
Compatible Networks	10/100/1000 Mbps
Industry Standards	IEEE 802.3at/af Power Over Ethernet, IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX, IEEE 802.3ab 1000BASE-TX, IEEE 802.3x Flow Control
PoE Output	52V DC, 30W (per-port)
Connectors	8 x RJ-45 Female
Maximum Data Transfer Rate	2 Gbps (Full-Duplex)
Switching Architecture	Store-and-Forward
Buffer Size	128 KB
Full Duplex	Yes
Auto MDIX	Yes
Flow Control	Half-duplex back-pressure and IEEE802.3x full-duplex
Power Consumption	120W Max
Power Adapter	52V DC, 2.5A
Enclosure Material	Steel
Operating Temperature	0°C to 55°C (32°F to 131°F)
Storage Temperature	-20°C to 90°C (-4°F to 194°F)
Humidity	10~90% RH (Non-Condensing)
Dimensions	188 x 119 x 38 mm

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit **www.startech.com/support** and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit **www.startech.com/downloads**

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.