

Version1.2



INDEX

Description	
Feature	
Connection Diagram	
Front Panel	5
Rear Panel	5
Dip Switch	6
Specifications	7
Firmware Upload	
Update List	10
Warranty	10


Description

The KanexPro next generation of SDI to HDMI converters are designed for connecting your professional SDI video equipment to any HDMI display or consumer based TV's. It accepts SD, HD or 3G-SDI signals and converts it to HDMI maintaining signal integrity of the original image and resolution. The converter also has two SDI loop output for sending re-clocked SDI signals and connecting to down-stream equipment.

Feature

- Get the highest quality 3G-SDI conversion to HDMI
- Supports 2-channel audio @20 bit,192 KHz audio
- Supports multiple video resolutions: SDI 525i, 625i
- HD: 720p 24, 25,30,50 & 60 Hz.
- HD: 1080i 50 & 60 Hz.
- HD: 1080p 24, 25,30, 50 & 60 Hz.
- Data rates up to 2.97 Gbps
- Supports conversion to SMPTE 425M Level A 1080p 50/59.94/60 4:2:2 10-bit
- SDI Input Cable Length Support up to 100m
- 3G mode length up to: 130m
- HD mode length up to: 170m
- SD mode length up to: 300m
- One-way SDI output with re-clock function
- Supports cascading of multiple SDI's in application
- Automatically switches between SD, HD and 3 Gb/s SDI standards
- Compact in size, perfect for mobile broadcasting units and users

Application Diagram



Front Panel



NO	Component	Function
1	SDI Output Port	From your SDI Display Device plug into these ports (Pass Through)
2	HDMI Output port	From your HDMI Display Device plug into this port.

Rear Panel



NO	Component	Function
1	Power Jack	The Power adapter plug into here.
2	Power/Locked LED	The LEDs is indicating Signal indicate
3	Dipswitch	Pin On (↑):Pin OFF (↓):EnableDisable1.Reclocker2.LED Mode3.NA.
4	SDI input Port	From your HDMI Source plug into these ports

Dip Switch

- Re-clock: Receives a signal and retransmits it at a higher level and/or higher power, or onto the other side of an obstruction, so that the signal can cover longer distances.
- LED Mode:

Pin OFF (\downarrow):

Resolution	SD LED	HD LED	3G LED	POWER LED
720 x 480i (NTSC)	0	0	0	•
720 x 576i (PAL)	0	0	•	0
1280 x 720 p50	0	0	•	•
1280 x 720 p60	0	•	0	0
1920 x 1080 i50	0	•	0	•
1920 x 1080 i60	0	•	•	0
1920 x 1080 p24	0	•	•	•
1920 x 1080 p25	•	0	0	0
1920 x 1080 p30	•	0	0	•
1920 x 1080 p50	•	0	•	0
1920 x 1080 p60	•	0	•	•
2048 x 1080 p24	•	•	0	0
2048 x 1080 p25	•	•	0	•
Un-know	0	0	0	0

• : LED ON

○ : LED OFF

Pin On (↑)

Resolution	3G LED	HD LED	SD LED
NTSC / PAL	0	0	•
720p / 1080i / 1080 [24p, 30p]	0	٠	0

1080 [50p,60p]	٠	0	0
● : LED ON			
○: LED OFF			
NA:			

Specifications

DESCRIPTION	
	SD – 720 x 480i / 720 x 576i
Support Video Resolution	HD– 1280 x 720 50p/60p
	1920 x 1080 50i/60i
	1920 x 1080 24p/25p/30p
	3G– 1920 x 1080 50p/60p
	SD-SDI (SMPTE 259M)
SDI format	HD-SDI (SMPTE 292M)
	3G-SDI (SMPTE 424M / SMPTE 425M)
Audio Support	2 Channel of Stereo
Re-clock Function	Yes (Dip Switch)
Coaxial Cable Type	RG6/RG59(75Ω)
	3G: 100m of RG6/ 86m of RG59
	HD: 170m of RG6/ 120m of RG59
Cable Equalization	SD: 400m of RG6/ 280m of RG59
	*1 RG6: CANARE L-5CFB Cable / RG59: Belden 9275 Cable
	*2 Cable Length Performance: Depending on SDI Signal and
	Cable Quality
Firmware Updates	
Input	1 x BNC [SDI]
Output	1 x HDMI
·	2 x BNC [SDI]
BNC Connector	3G 75 Ω inter-locked socket
HDMI Connector	TYPE A [19-pin female]
DIP Switch	3-pin [Re-clock / LED mode / NA]
Housing	SECC
Dimension	L:104mm x W:63.3mm xH:26mm
Power Source	Power Adapter: AC 100 ~ 240 V/DC (+6 ~ 15 V)
Operation Temperature	0~50°C [32~114°F]
Storage Temperature	-20~+60°C

Firmware Upload

• Firmware is upgradable in the field using the integrated USB port

How to Firmware upgrade:

Step 1.

Open Upload Firmware Program tools.exe and connect box to PC by USB Cable.

🧠 Upload Firr	nware Program tools
Connection d	Discourse stand
Load file File name: File size:	C:\Documents and Settings\Navan\点面\Converter Box\TestProgram\Upload Fir Open File Checksum: Save
Status	Start

Step 2.

Plug and un-plug "DC adapter" to power on/off the converter box (the connection check status will be changed to "Connect")

🧠 Upload Firm	nware Program tools	
Connection ch	Discourse sheet	
Load file File name: File size:	C:\Documents and Settings\Navan\桌面\C	Converter Box\TestProgram\Upload Fir Open File Checksum: Save
Status		Start

Step 3.

Plug and un-plug "DC adapter" again (the connection check status will be changed to "Connected") and Please click the Open File button to select the firmware bin file.

🧠 Up	load Firm	vare Program tool	3			
	Disconne	Conn	ected			
File	e name: e size:	C:\Documents and S 14292 Bytes	ettings\Navan\桌面\Coi]	nverter Box\Bi Checksum:	n\SDI2HD\1.7(2011.1 0x6BB8	Open File
Sta	itus]	Start	

Step 4.

Please click "Start' Button to proceed with new firmware programming. The PASS message will appear when the procedures finished.

Connection c		nnected	
Load file File name: File size:	C:\Documents and Sel 62520 Bytes	tings\Navan\桌面\Converter Box\B Checksum :	iin\SDI2HD-S\BUTTON\ Open File 0x1AD2
Status			Start PASS

Step 5.

Close Upload Firmware Program tools

Connection d	Discourse at a d
Load file File name: File size:	C:\Documents and Settings\Navan\点面\Converter Box\TestProgram\Upload Fit Open File Checksum: Save
Status	Start

Update List

Data	Version	Command
2013.03.14	V1.1	1. Modify Cable Equalization
2015.03.20	V1.2	1. Change Box Pic

Warranty

A. LIMITED WARRANTY

KanexPro \mathbb{M} warrants that (a) its products (the "Product") will perform greatly in agreement with the accompanying written materials for a period of 36 months (3 full years) from the date of receipt and (b) that the product will be free from defects in materials and workmanship under normal use and service for a period of 3 years.

B. CUSTOMER REMEDIES

KanexPro's entire liability and Customer's exclusive remedy shall be, at KanexPro option, either return of the price paid for the product, or repair or replacement of the Product that does not meet this Limited Warranty and which is returned to KanexPro with a copy of customers' receipt. This Limited Warranty is void if failure of the Product has resulted from accident, abuse, or misapplication. Any replacement Product will be warranted for the remainder of the original warranty period of 3 years, whichever is longer.

C. NO OTHER WARRANTIES

To the maximum extent permitted by applicable law, KanexPro disclaims all other warranties, either express or implied, including, but not limited to implied warranties of merchantability and fitness for a particular purpose, with regard to the product and any related written materials. This limited warranty gives customers specific legal rights. Customers may have other rights depending on the jurisdiction.

D. NO LIABILITY FOR DAMAGES

To the maximum extent permitted by applicable law, in no event shall KanexPro be liable for any damages whatsoever (including without limitation, special, incidental, consequential, or indirect damages for personal injury, loss of business profits, business interruption, loss of business information, or any other pecuniary loss) arising out of the use of or inability to use this product, even if KanexPro has been advised of the possibility of such damages.



1405 pioneer street Brea, CA 92821