

RM41300G




4U High Performance Industrial Server Chassis

- Supports 8-slot rear window for 4 GPU cards (RM41300-FS81)
- Truly isolated anti-vibration design on internal HDD cage and drive cage
- Optional second 3 x 5.25" drive cage for maximum configuration flexibility
- Dedicated 80 mm fan for HDD cooling
- PCI-e card retainer to hold low profile and full height add-in cards (RM41300)
- Supports stand-alone installation via optional kit (RM41300)
- Supports 1-door or 2-door front bezel configuration (RM41300)



Specifications

| | |
|-------------------------------|---|
| M/B Form Factor | • Extended ATX (12" x 13") |
| Dimension (D x W x H) | • With front bezel: 563.7 x 430.0 x 176.0 (mm) 22.19" x 16.93" x 6.93" • Without front bezel: 543.7 x 430.0 x 176.0 (mm) 21.41" x 16.93" x 6.93" |
| Drive Bay | • Exposed: 3 x 5.25", 1 x 3.5", 1 x Slim ODD; Internal: 4 x 3.5" |
| HDD Backplane | • N/A |
| PSU Form Factor | • PS/2 Single or Mini-redundant |
| Indicators | • 1 x Power Status, 1 x HDD Activity, 2x LAN Activity |
| Front Control | • Power On/Off, System Reset, 2 x USB2.0/USB3.0(Optional) |
| Cooling Fans | • Front: 1 x 120 (mm) (T = 25 mm), PWM, Rear: 2 x 80 (mm) (T = 25 mm)(Option) |
| System Security | • Intrusion Switch, Key Lock on Front Door |
| Expansion Slot Opening | • 7,8 (RM41300G) or 15 x Full Height and Full Length |
| Net Weight | • 12.5 kg |
| Gross Weight | • 15.5 kg |
| Cubic Feet | • 4.03 |
| Container Loading | • 20': 245, 40': 524, 40'H: 592 (Single Packing) |



GPGPU

Equipped with truly isolated anti-vibration drive cages, dust-proof filter, and reliable add-on card holder make it ideal for high performance IPC. Supports 8-slot rear window for 4 GPU cards.