



# Haley Recliner



Goes Great with Work.®



Comfort and versatility have been designed into the **Haley** recliner from the ground up. Comfort is provided through a body activated recliner mechanism housed in a streamlined frame. A multitude of options provide the versatility to make **Haley** at home in a wide variety of settings from lobbies and lounges to patient rooms.

Recovery has never felt so good.

#### Standard Features

- Three position (24°, 35°, 52° recline) push arm mechanism
- Sinuous wire spring suspension and high density foam for durability and patient comfort
- Full length foot rest supports the entire leg
- Hardwood feet offered in a variety of finishes
- Standard widths rated to 350 lbs.
- Pillow back models include repositionable pillow
- Warranty: Limited lifetime on seating components; Three years on recliner mechanism

#### Additional Options

- IV pole and holder
- 3" non-marking casters offers mobility for cleaning or furniture rearranging
  - Front casters lock
  - Factory installation only
- Two color upholstery combinations available
  - Seat/Back: First fabric
  - Arms: Second fabric
  - (Cover photo fabric combination requires a custom quote)
- Clear vinyl headrest covers for non-pillow back models

#### Dimensions

29"W (Models 840, 845)  
 33"W (Models 843, 847)  
 37.5"D (70" Reclined)  
 46.75"H



**840C**

Seat/Back: Punch PN-014 Denim  
 Arms: Punch PN-023 Aqua

Shown on front:

**840**

WAL Walnut

Back/Seat: Round N' Round WC762-009 Lantern CRYPTON®

Outside Arms: Agora 306-023 Pistachio



#### Arm Caps

Black polyurethane or wood arm caps (available in 11 standard finishes) which match the standard feet.



#### Folding Side Table

Optional side table locks solidly in place yet easily folds flat.



#### Large Tablet Arm

Large tablet arm on brushed aluminum single pivot mechanism.



#### Pillow Back

Tufted look pillow back on 845 and 847.



#### Bariatric Widths

24.5" inside clearance rated at 500 lb. capacity.



#### Small Tablet Arm

Small tablet arm on brushed aluminum double articulating mechanism.



#### Heat & Massage

Operated through push-button control located on inside of arm (not available on pillow back models).



**840**

Expo 962 Leaf

082011 Haley

