THZ850GL



Click-In[™] Case for iPad® (9th, 8th and 7th Gen.) 10.2-inch, iPad Air® 10.5-inch, and iPad Pro® 10.5-inch, Black

- · Passes military grade 4' drop testing*
- Elastic strap closure for secure travel
- · Patented custom-molded tray for enhanced protection
- Infinite viewing angles and comfortable typing position
- · Precision-cut access to controls, ports and camera
- Patent-protected multi-generation tray flexes to fit iPad® (8th and 7th Gen.), iPad Air® 10.5-inch and iPad Pro® 10.5-inch
- Integrated holder for Apple Pencil or stylus (Pencil sold separately by Apple)
- · Limited Lifetime Warranty

MSRP	\$34.99													
Color	Black													
Device Compatibility	Apple: iPad 10.2" 9th Gen, iPad 8th Gen, iPad 7th Gen, iPad Air 10.5" and iPad Pro 10.5"													
Warranty	Limited	Limited Lifetime Warranty												
UPC Code	092636344115													
Product Dim. (L W H)	10.00"	Х	7.15"	Χ	0.71"	•	C).84	lb.					
Packaged Dim. (L W H)	7.30"	Х	0.85"	Х	11.50"	:	C).96	lb.	:	Qty	1		
Inner Carton Dim. (L W H)	8.10"	Х	5.59"	Χ	12.50"	:	5	5.32	lb.	:	Qty	5		
Master Carton Dim. (L W H)	8.10"	Х	5.59"	Χ	12.50"	•	5	5.32	lb.	:	Qty	5		
Country of Origin	CNI / TAA Compliant: No													
HTS: ECCN	3926.10	3926.10.0000						: EAR99						
Logoable	TBD													

The Click-In™ Case for iPad® (8th and 7th Gen.) 10.2-inch, iPad Air® 10.5-inch, and iPad Pro® 10.5-inch provides strong, military-grade drop protection in a lightweight, ultra-slim design. It has durable front and back covers, with soft lining inside that safeguards the device screen from scratches. With a wrap-around bezel and reinforced corners, the tray clicks securely around your tablet's back and sides.

The front cover flips back to transform into a hands-free stand so that it's easy to view and comfortable to type on your tablet. And, precision cut holes enable you to access all the ports and camera without taking off the case. Altogether, it's a superior choice for protecting your iPad.

*As tested by an independent third party applying MIL-STD-810G, Method 516.6, Procedure IV. Additional Downloads